MASTERYS BC+

Designed for easy integration and use

from 10 to 160 kVA



A flexible and cost-effective solution

- A compact range of standard product references with a variety of add-on options to adapt to every customer's site.
- Easy to configure for retrofit in existing installations.
- Equipped with manual bypass breaker in standard mode.

Long back-up time engineered-in

- Several optimised choices for standard internal battery configuration.
- Increased internal battery density for reduced footprint and simplified installation.
- Internal basic back-up time available up 80 kVA, without additional external battery cabinet.
- High recharging current option for very long back-up time.

Embedded digital technology

- Digital Native UPS generation.
- IoT ready device for access to connected services.
- Easy integration in LAN/WAN and virtual environments.

Fast and easy installation

- A wide range of UPS from 10 to 160 kVA with the same performance and functionality.
- Free eRULER online sizing tool to get dimensions and electrical information in advance before installation.
- Tutored UPS installation with eWIRE mobile app.
- Quickly get online product documentation by simply inputting the Serial Number.

Fast delivery

- "Fast track manufacturing" option available for urgent projects or last-minute requirements.
- Fast delivery even for highly customised configurations thanks to easily combined options.

User and environmentally friendly

- 25+ languages available in the mimic panel.
- Ergonomics designed to simplify usage.Anticipates eco-regulations and is RoHS
- Anticipates eco-regulations and is Recompliant.
- Units provided with wheels for easy positioning.

The solution for

- SME IT networking / computer rooms
- Control rooms
- > Emergency service
- > Payment systems
- > Public sector
- Security control

Certifications and attestations







Expert Services





MASTERYS BC+ Three-phase UPS from 10 to 160 kVA

System features

- Dual input mains (30-120 kVA).
- Internal maintenance bypass switch.
- Output switch breaker.
- Auxiliary mains switch breaker.
- Backfeed protection: detection circuit.
- Full compatibility with generators.
- Internal normal-life batteries up to 80 kVA.

Remote monitoring and cloud services

- SoLink: Socomec 24/7 remote monitoring service connecting your installation to the nearest Socomec Service Centre.
- SoLive UPS: mobile app enabling the monitoring of the UPS systems from a smartphone.

Standard communication features

- 3.5" multilanguage graphic display.
- 2 slots for communication options.
- USB port for downloading log file.
- Ethernet port for service purposes.


Communication options

- Dry-contact interface
- (configurable voltage-free contacts).
- MODBUS RTU RS485 or TCP.
- PROFIBUS gateway.BACnet/IP interface.
- NET VISION: professional WEB/ SNMP Ethernet interface for secure UPS monitoring and remote automatic shutdown.
- REMOTE VIEW PRO supervision software.
 IoT Gateway for Socomec cloud services
- and SoLive UPS mobile app.Remote touch-screen panel.

System options

- 3-phase input without neutral.
- Internal backfeed isolation device.
- Common mains coupling bars.
- TN-C grounding system.
- ACS synchronisation system.
- IP21 degree of protection.
- Long life internal batteries up to 80 kVA.
- High capacity battery charger.

UPS dimensions (WxDxH)



Technical data

	MASTERYS BC+										
Sn [kVA]	10	15	20	30	40	60	80	100	120	160	
Pn [kW]	10	15	20	30	40	60	72	90	108	144	
Input / output 3/1	•	•	•	-	-	-	-	-	-	-	
Input / output 3/3	•	•	•	•	•	•	•	•	•	•	
Parallel configuration	up to 6 units ⁽¹⁾										
INPUT											
Rated voltage	400 V 3ph+N (3 wire input also available on demand)										
Voltage tolerance	240 V to 480 V										
Rated frequency		40-70 Hz									
OUTPUT											
Rated voltage	1ph + N: 230 V (can be configured 220/240 V) 3ph + N: 400 V (can be configured 380/415 V)										
Rated frequency	50/60 Hz										
EFFICIENCY											
Double conversion VFI mode	up to 95%										
Eco Mode		up to 99%									
BATTERY											
Technologies	VRLA, NiCd										
INTERNAL BACK-UP TIME (MINUTE	ES) ⁽²⁾									
COMPACT B3	22	13	9				-				
COMPACT M3	35	22	15				-				
M4	101	66	46	28	20			-			
S4		-		9	6			-			
Т6			-			13	9		-		
ENVIRONMENT											
Operating ambient temperature		up to +35 °C									
UPS CABINET											
Weight	depends on the number of batteries installed - contact us										
Degree of protection	IP20 (IP21 on demand)										
Colours		metallised grey E150HVR									
STANDARDS											
Safety	IEC/EN 62040-1										
EMC	IEC/EN 62040-2										
Performance		EN 62040-3									
Environmental		full compliance with the RoHS EU directive									
Product declaration		CE, EAC, UKCA									

(1) Up to 4 units for MASTERYS BC+ compact (2) @80% of rated power with load PF 0.9.

