

95534063

Automatic transfer switch ATyS g 4P 630A



Strong points

- Rapid commissioning
- Specifically designed for mains/mains and mains/genset applications
- RS485 communication
- Watchdog relay to check product availability
- Integrated auxiliary contacts
- Extended power supply range
- More robust

General characteristics

- Range from 125A to 3200A.
- Available in 3P or 4P.
- Extended power supply range 166-332VAC.
- Rapid commissioning.
- ATS with integrated DPS and controller for functions dedicated to mains/mains applications.
- Robust design.
- Optional RS485 communication module.

Compliance with standards

- IEC 60947-6-1
- IEC 60947-3
- GB/T 14048.11

Link to the reference

<https://apac.socomec.com/en/reference/95534063>

ATyS g are 3 or 4 pole automatic transfer switches, with positive break indication. They incorporate all the functions offered by the ATyS r, as well as functions intended for mains/mains and mains/genset applications. In automatic mode they enable the monitoring of, and the on-load changeover between, two power supply sources, in accordance with the parameters configured via potentiometers and DIP switches. Remote monitoring of the ATyS g is possible with the optional RS485 communication module. They are intended for use in low voltage power supply systems where a brief interruption of the load supply is acceptable during transfer.

----- System -----	
Fill rate E-Order Common	86
Fill rate E-Order Selection	100
Classification	
UNSPSC	39122205
ETIM Class	EC000216
IGCC	5177
Commerce	
Effective date	2012-06-21
Country of origin	FR
Discount Policy	1CB76
Discount Policy Label	ATYS T & G
Length of the product unit	0.26
Width of the product unit	0.437
Depth of the product unit	0.3205
Weight	18.4
ETIM - Electrical characteristics	
Max. rated operation voltage Ue AC [V]	1000
Rated operating voltage [V]	400..690
Rated permanent current Iu [A]	630
Rated permanent current at AC-23, 400 V [A]	630
Rated permanent current at AC-21, 400 V [A]	630
Rated short-time withstand current Icw [kA]	10
Switching power at 400 V [kW]	5040
Conditioned rated short-circuit current Iq [kA]	50
Number of poles	4
ETIM - Mechanical characteristics	
Suitable for floor mounting	No
Suitable for front mounting 4-hole	No
Suitable for front mounting centre	No
Suitable for distribution board installation	No
Suitable for intermediate mounting	Yes
Colour control element	Other
Degree of protection (IP), front side	IP20
ETIM - Technical features	
Version as main switch	Yes
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	No

Version as reversing switch	Yes
Number of switches	2
Number of auxiliary contacts as normally open contact	3
Motor drive optional	No
Motor drive integrated	Yes
Voltage release optional	No
Device construction	Built-in device fixed built-in technique
Type of control element	Other
Interlockable	Yes
Type of electrical connection of main circuit	Bolt connection

Logistics

GTIN/EAN	3596032775834
Customs number	8536508090
Price unit	PC
Weight of the packing unit	18.8
Length of the packing unit	0.534
Width of the packing unit	0.42
Depth of the packing unit	0.37

Norms

Conformity to standards	CCC IEC
-------------------------	-------------

Technical Characteristics

Control operator	Automatic programmable for GENSET
Number of poles	4
Rated current	630
Type	Class PC
Frame size	B5